



## InGaAs Ultra-Low Noise Balanced Detector

200M



- **Product Description**

The UBD series ultra-low noise balanced detector module are upgraded products based on the previous MBD series. Compared to the original MBD series, the background noise is significantly reduced under the same

conditions. With the same bandwidth and gain, the background noise of the UBD series is approximately one-third of that of the MBD series modules, resulting in higher sensitivity and better signal-to-noise ratio.

- **Product features**

Ultra-low noise、 High Gain、 High bandwidth、 Compact structure、 Built-in low-noise isolation power supply

- **Part Number**

MP-UBD-M-I-200-F/S-A

- **Application area**


Distributed fiber optic sensing、 Laser wind radar、 Optical coherence tomography、 Spectral measurement、 Pulsed light detection

- **Core parameters**

| Wavelength | Bandwidth | Responsivity |
|------------|-----------|--------------|
| 800-1700nm | 200MHz    | 0.95A/W      |



- **Dimension Drawing**



## ● General Parameters

Parameter



|                             |          |       |       |       |       |       |      |       |       |      |       |            |
|-----------------------------|----------|-------|-------|-------|-------|-------|------|-------|-------|------|-------|------------|
| Detect or type              | InGaAs   |       |       |       |       |       |      |       |       |      |       |            |
| Wavelength                  | 800~1700 |       |       |       |       |       |      |       |       |      |       | nm         |
| Bandwidth                   | 100 M    | 200 M | 300 M | 400 M | 500 M | 800 M | 1G   | 1.2 G | 1.5 G | 2G   | 2.5 G | Hz         |
| Detect or responsiveness    | 0.95     | 0.95  | 0.95  | 0.95  | 0.95  | 0.95  | 0.95 | 0.95  | 0.95  | 0.95 | 0.95  | A/W@1550nm |
| Transimpedance gain         | 30K      | 30K   | 30K   | 20K   | 10K   | 30K   | 30K  | 30K   | 30K   | 30K  | 30K   | V/W        |
| Maximum input optical power | 140      | 140   | 140   | 210   | 420   | 140   | 140  | 140   | 140   | 140  | 140   | μW         |




|                             |       |       |       |       |     |     |     |     |     |     |     |                 |
|-----------------------------|-------|-------|-------|-------|-----|-----|-----|-----|-----|-----|-----|-----------------|
| NEP                         | 2.5   | 2.5   | 2.5   | 2.9   | 3.1 | 3.1 | 3.1 | 3.1 | 3.1 | 3.1 | 3.1 | pW/S<br>qrt(Hz) |
| Common mode rejection ratio | >30   | >30   | >30   | >30   | >30 | >30 | >30 | >30 | >30 | >30 | >30 | dB              |
| Output impedance            | 50    | 50    | 50    | 50    | 50  | 50  | 50  | 50  | 50  | 50  | 50  | Ω               |
| Output coupling mode        | DC/AC | DC/AC | DC/AC | DC/AC | DC  | AC  | AC  | AC  | AC  | AC  | AC  |                 |
| Supply voltage              | 5     | 5     | 5     | 5     | 5   | 12  | 12  | 12  | 12  | 12  | 12  | V               |




|                |                              |        |        |        |        |        |        |        |        |        |        |    |
|----------------|------------------------------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|----|
| Supply current | 0.5(x)                       | 0.5(x) | 0.5(x) | 0.5(x) | 0.5(x) | 0.5(x) | 0.5(x) | 0.5(x) | 0.5(x) | 0.5(x) | 0.5(x) | A  |
| Optical input  | FC/APC (Free space optional) |        |        |        |        |        |        |        |        |        |        |    |
| RF output      | SMA                          |        |        |        |        |        |        |        |        |        |        |    |
| Dimensions     | 80*90*25                     |        |        |        |        |        |        |        |        |        |        | mm |

## Test result



300 MHz bandwidth response curve



**Comparison of the baseline noise between ultra-low noise balanced detectors  
and conventional balanced detectors**