

## 7.4um Low-Power Benchtop DFB-QCL Mid-Infrared Quantum Cascade Laser 5mW (Benchtop Light Source)



### ● Product Description

QCL7400 - 7.4um low-power benchtop DFB-QCL mid-infrared quantum cascade laser is a domestically advanced ultra-low-power QCL DFB laser developed by Idealphotonics in the first half of 2018. The tunable range exceeds 100nm, and the output power is greater than 20mw to meet the industrial needs of customers testing gas sensors. Our laser collimated output has stable output power and high temperature and wavelength



stability, which is several orders of magnitude higher than the stability of traditional high-power quantum cascade lasers. It provides an excellent test light source for our mid-infrared test customers.

## ● Product features

Low power consumption, high power, High side mode suppression ratio, Intelligent software control, Small structure

## ● Part Number

MP-QCL-7400-DFB-5-B

## ● Application area

TDLAS CO high-precision trace analysis, Mid-infrared test light source

## ● Core parameters

Peak wavelength	Spectral width	Output power	Laser type
7.4μm	1MHz	5mW	QCL-DFB

## ● General Parameters

Parameter

Parameter	Unit	Indicators		
		Min.	Typical value	Max.



<b>Output power 1</b>	<b>mW</b>		<b>5</b>	
<b>Peak operating wavelength 2</b>	<b>um</b>		<b>7.4</b>	
<b>Spectral width (FWHM)</b>	<b>MHZ</b>		<b>1</b>	
<b>Output side mode suppression ratio (SMSR)</b>	<b>dB</b>	<b>20</b>		
<b>Output isolation 3</b>			<b>30</b>	
<b>Wavelength temperature coefficient</b>	<b>Mrad</b>		<b>0.6</b>	
<b>Wavelength current coefficient</b>	<b>mm</b>		<b>0.2</b>	
<b>Output power stability (8 hours) 4</b>	<b>nm/A</b>		<b>±1</b>	<b>±4</b>
<b>Output power adjustable range</b>	<b>%</b>	<b>0</b>		<b>100</b>
<b>TEC operating range</b>	<b>°C</b>	<b>0</b>		<b>50</b>
<b>Operating voltage</b>	<b>VAC</b>	<b>100</b>	<b>220</b>	<b>240</b>
<b>Operating temperature</b>	<b>°C</b>	<b>0</b>	<b>-</b>	<b>55</b>
<b>Storage temperature</b>	<b>°C</b>	<b>-20</b>	<b>-</b>	<b>65</b>
<b>Specifications and dimensions</b>	<b>mm</b>	<b>290(L)×108(W)×68(H) mm</b>		




## Technical Specifications

1. Output power is optional;
2. Peak operating wavelength can be specified;
3. Output power stability test condition is 25 degrees, after 30 minutes of preheating;
4. Maximum power consumption refers to the overall power consumption under extreme working conditions;




## Measured spectrum






## Wavelength temperature tuning curve




## Power stability




## QCL laser characteristic curve (taking 7.4um typical wavelength as an example)


### Output power characteristic curve:




### Voltage characteristic curve



## TEC current characteristic curve










## TEC voltage characteristic curve







## Laser spectrum (CW)






### Wavelength temperature current tuning curve




## Quantum cascade laser output spot










The pixel size of the test camera is 5  $\mu\text{m}$ , and the Gaussian fitting spot diameter is 320  $\mu\text{m}$ .

## Simulation results of absorption spectral lines near 7.4um




## The relationship curve between peak wavelength and current





## Control software





## Ordering Information

MP-QCL- W □-☆-△-XX

W□□□□: Wavelength

7400: 7400nm

10530: 10530nm

☆: collimator

1: with

0: without

△: laser type

FP: QCL-FP

DFB: QCL-DFB

XX: output power

005=5mw

010=10mw

100=100mw